

170-22000



Article Number: 170-22000

Helagaine Braided Sleeving, 20.0 mm Dia, Polyamide 6.6, Gray, 164ft/Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-22000

Type HEGPA6620

Color Gray (GY)

Features and Benefits

- Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture.
- Material performs well in wet applications and where abiding substrate has a smooth surface.

Product Description Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

Short Description Helagaine Braided Sleeving, 20.0 mm Dia, Polyamide 6.6, Gray, 164ft/Reel

Product Dimensions

Length L (Imperial) 164.0 ft

Length L (Metric) 50.0 m

Reel Length (imperial) 164.0 ft

Bundle Diameter Min. (Imperial) 0.59 "

Bundle Diameter Min. (Metric) 15 mm

Bundle Diameter Max. (Imperial) 0.91 "

Bundle Diameter Max. (Metric) 23 mm

Nominal Diameter (Imperial) 3/4 "

Nominal Diameter (Metric) 20 mm

Braid Density n. 85%

Logistics and Packaging

Quantity Per metre

Package Quantity (Metric) 50 m

Carton Quantity 50 Meter

Weight (Metric) 1.4 kg

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability FMVSS 302
UL94 V2

Halogenfree Yes

Operating Temperature -76°F to +302°F (-60°C to +150°C)

ROHS Compliant Yes

Certification/Specification EN 45545: 2013