HellermannTyton

170-22500

Article Number: 170-22500

Helagaine Braided Sleeving, 25.0 mm Dia, Polyamide 6.6, Gray, 164.0 ft/Reel

RoHS

Download drawing Download spec sheet

Base Data

Local Order Number	170-22500
Type	HEGPA6625
Color	Gray (GY)
Features and Benefits	• Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture. • Material performs well in wet applications and where abiding substrate has a smooth surface.
Product Description	Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.
Short Description	Helagaine Braided Sleeving, 25.0 mm Dia, Polyamide 6.6, Gray, 164.0 ft/Reel

Product Dimensions

Length L (Imperial)	164.0 ft
Length L (Metric)	50.0 m
Reel Length (imperial)	164.0 ft
Bundle Diameter Min. (Imperial)	0.71 "
Bundle Diameter Min. (Metric)	18 mm
Bundle Diameter Max. (Imperial)	1.1 "
Bundle Diameter Max. (Metric)	28 mm
Nominal Diameter (Imperial)	1 "
Nominal Diameter (Metric)	25 mm
Braid Density	n. 85%

Logistics and Packaging

Quantity Per	metre
Package Quantity (Metric)	50 m
Carton Quantity	50 Meter
Weight (Metric)	1.8 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	FMVSS 302 UL94 V2
Halogenfree	Yes

Operating Temperature	-76°F to +302°F (-60°C to +150°C)
ROHS Compliant	Yes
Certification/Specification	EN 45545: 2013

© HellermannTyton 2015