

2.5NFP0C



Article Number: 161-05024

Spiralwrap, 3/8" Diameter, PE, Black, 100ft/RL

 RoHS

 Download spec sheet

Base Data

Local Order Number	2.5NFP0C
Type	2.5NFP
Color	Black (BK)
Features and Benefits	• Sheathing allows flexible routing and lead-out of cables • The inner edges are beveled preventing damage to cables • Sheathing is reusable and resistant to most chemicals • Spiralwrap is U.L. Recognized
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap, 3/8" Diameter, PE, Black, 100ft/RL

Product Dimensions

Length L (Imperial)	100.0 ft
Length L (Metric)	30.48 m
Reel Length (imperial)	100.0 ft
Variant	Spiral Binding
Bundle Diameter Min. (Imperial)	0.31 "
Bundle Diameter Min. (Metric)	7.92 mm
Bundle Diameter Max. (Imperial)	3.0 "
Bundle Diameter Max. (Metric)	76.2 mm
Diameter D (imperial)	0.375 "
Diameter D (metric)	9.53 mm
Nominal Diameter (Imperial)	3/8 "
Nominal Diameter (Metric)	9.53 mm
Wall Thickness WT (Imperial)	0.052 "
Wall Thickness WT (Metric)	1.32 mm
Pitch (imperial)	0.438 "
Pitch (metric)	11.13 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	100.0 ft
Package Quantity (Metric)	30.48 m
Carton Quantity	100.0 ft

Material and Specifications

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Flammable
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes