



558-00338



Article Number: 558-00338

Solid Colored Continuous Roll, 3.0" X 250', Vinyl, Orange, 250ft/RL

 RoHS

 Download spec sheet

Base Data

Local Order Number	558-00338
Type	HT3OE250
Color	Orange (OG)
Features and Benefits	<ul style="list-style-type: none">• Continuous Vinyl Labels are made with UV stable materials for long outdoor life.• Labels are extruded in the actual color and not colored using surface inks for long term fade resistance.• Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal trasnfer printing systems.
Product Description	HellermannTyton continuous vinyl labels come in a variety of colors and printing widths. The viny is UV stable and has been tested to 20 years outdoor durability in Xenon Arc testing. The labels can be printed and cut to any length to create a wide variety custom label designs, on demand and using standard thermal transfer printing equipment. Each roll contains 250 feet (76M) of high performance vinyl.
Short Description	Solid Colored Continuous Roll, 3.0" X 250', Vinyl, Orange, 250ft/RL

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Width W (Imperial)	3.0 "
Width W (Metric)	76.2 mm
Height H (Imperial)	3.0 "
Height H (Metric)	76.2 mm
Print Method	Thermal Transfer
Vertical Repeat VR (metric)	76.2 mm
Vertical Repeat VR (imperial)	3.0 "
Width of Liner WL (imperial)	3.0 "
Width of Liner WL (metric)	76.2 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	250
Package Quantity (Metric)	250 ft
Labels per Column	1
Labels per Row	1

Material and Specifications

Material	Vinyl
----------	-------

Material Shortcut VL

Adhesive Shortcut Acrylic

Adhesive Acrylic

Adhesive Operating Temperature -40°F to +180°F (-40°C to +82°C)

Operating Temperature -40°F to +180°F (-40°C to +82°C)

ROHS Compliant Yes