



558-00370



Article Number: 558-00370

Solid Colored Continuous Roll, 4.0" X 250', Vinyl, Red, 250ft/RL

 RoHS

 Download spec sheet

Base Data

Local Order Number	558-00370
Type	HT4RD250
Color	Red (RD)
Features and Benefits	<ul style="list-style-type: none">• Continuous Vinyl Labels are made with UV stable materials for long outdoor life.• Labels are extruded in the actual color and not colored using surface inks for long term fade resistance.• Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal trasnfer printing systems.
Product Description	Continuous Vinyl Labels are made with UV stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long term fade resistance. The Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.
Short Description	Solid Colored Continuous Roll, 4.0" X 250', Vinyl, Red, 250ft/RL

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Width W (Imperial)	4.0 "
Width W (Metric)	101.6 mm
Height H (Imperial)	4.0 "
Height H (Metric)	101.6 mm
Print Method	Thermal Transfer
Vertical Repeat VR (imperial)	4.0 "
Vertical Repeat VR (metric)	101.6 mm
Width of Liner WL (metric)	101.6 mm
Width of Liner WL (imperial)	4.0 "

Logistics and Packaging

Quantity Per	reel
Package Quantity	250
Package Quantity (Metric)	250 ft
Labels per Column	1
Labels per Row	1

Material and Specifications

Material	Vinyl
----------	-------

Material Shortcut VL

Adhesive Acrylic

Adhesive Shortcut Acrylic

Adhesive Operating Temperature -40°F to +180°F (-40°C to +82°C)

Halogenfree Yes

Operating Temperature -40°F to +180°F (-40°C to +82°C)

ROHS Compliant Yes