

558-00377



**Article Number:** 558-00377

**Solid Colored Continuous Roll, Reflective, 1.0" X 250', Vinyl, Red, 250ft/RL**



Download spec sheet

## Base Data

**Local Order Number** 558-00377

**Type** rdl250l

**Color** Red (RD)

**Features and Benefits**

- Continuous Vinyl Labels are made with UV stable materials for long outdoor life.
- Labels are extruded in the actual color and not colored using surface inks for long term fade resistance.
- Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

**Product Description** Continuous Vinyl Labels are made with UV stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long term fade resistance. The Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

**Short Description** Solid Colored Continuous Roll, Reflective, 1.0" X 250', Vinyl, Red, 250ft/RL

## Product Dimensions

**Length L (Imperial)** 250.0 ft

**Length L (Metric)** 76.2 m

**Width W (Imperial)** 1.0 "

**Width W (Metric)** 25.4 mm

**Height H (Imperial)** 1.0 "

**Height H (Metric)** 25.4 mm

**Print Method** Thermal Transfer

**Vertical Repeat VR (metric)** 25.4 mm

**Vertical Repeat VR (imperial)** 1.0 "

**Width of Liner WL (metric)** 25.4 mm

**Width of Liner WL (imperial)** 1.0 "

## Logistics and Packaging

**Quantity Per** reel

**Package Quantity** 250

**Package Quantity (Metric)** 250

**Labels per Column** 1

**Labels per Row** 1

## Material and Specifications

**Material** Vinyl

**Material Shortcut** VL

**Adhesive Operating Temperature** -40°F to +176°F (-40°C to +80°C)

**Operating Temperature** -40°F to +176°F (-40°C to +80°C)

**ROHS Compliant** Yes

**UL Recognized (US)** No