



ET330



Article Number: 904-00007

Electrical Tape, Thickness 7.0 mil, PVC, Black, 10 Rolls/pkg

 Download spec sheet

Base Data

Local Order Number	ET330
Type	ET33
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"><li>• PVC Tape is ideal for general purpose electrical applications.</li><li>• Heavy duty tape is comfortable and has exceptional surface and adhesive characteristics.</li><li>• Fast, easy and economical way to cable splicing, terminating and wire insulating.</li></ul>
Product Description	Electrical tapes are heavy duty vinyl and ideal for general purpose applications. Tape provides a fast, easy and economical way to cable splicing, terminating, wire insulating, and more. These comfortable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof.
Short Description	Electrical Tape, Thickness 7.0 mil, PVC, Black, 10 Rolls/pkg

Product Dimensions

Length L (Imperial)	33.0 ft
Length L (Metric)	10.06 m
Width W (Imperial)	0.75 "
Width W (Metric)	19.05 mm
Thickness T (Imperial)	7.0 mil

Logistics and Packaging

Quantity Per	reel
Package Quantity	10
Package Quantity (Metric)	10
Carton Quantity	200

Material and Specifications

Material	Flexible Polyvinyl Chloride (PVC)
Material Shortcut	PVC
US MILSPEC	MIL-1-7798-A
Adhesion	16 oz./inch
Operating Temperature	+20°F to 176°F (-7°C to +80°C)
UL Listed (US)	Yes
UL Listed (US and Canada)	No
UL Recognized (US)	Yes

UL Recognized (US and Canada) No