

## T5D100010H4



**Article Number:** 211-00119

**P Clamp, .5" Width, 1.0" Max Bundle Dia, .203" Mounting Hole Dia, PA66, White, 500/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** T5D100010H4

**Type** T5D1000

**Color** White (WH)

**Features and Benefits**

- Easily guide and locate wire and cables up to 1.5" in diameter.
- Designed with a radiused edge to prevent chaffing and cutting into insulation.

**Product Description** HellermannTyton P Clamps easily guide and locate wires and cables. The clamps are designed with a radiused edge to prevent chaffing and cutting into insulation. Available sizes up to 1.5" bundle diameters.

**Short Description** P Clamp, .5" Width, 1.0" Max Bundle Dia, .203" Mounting Hole Dia, PA66, White, 500/pkg

### Product Dimensions

**Fixation Method** screw-hole

**Variant** Closed

**Width W (Imperial)** 0.5 "

**Width W (Metric)** 12.7 mm

**Bundle Diameter Max. (Imperial)** 1.0 "

**Bundle Diameter Max. (Metric)** 25.4 mm

**Mounting Hole Diameter D (Imperial)** 0.203 "

**Mounting Hole Diameter D (Metric)** 5.1 mm

**Wall Thickness WT (Imperial)** .050 "

**Wall Thickness WT (Metric)** 1.3 mm

**Mounting Hole Centers (Imperial)** 0.91 "

**Mounting Hole Diameter D Max.** 5.1 mm

**(Metric) Mounting Hole Diameter D Min. (Metric)** 5.1 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 500 Pieces

### Material and Specifications

**Material** Polyamide 6.6 (PA66)

**Material Shortcut** PA66

**Flammability** UL94 V2

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

**ROHS Compliant** Yes

**UL Recognized (US and Canada)** Yes

---

© HellemanTyton 2015