

TAG1-100

Article Number: 595-01100

Dot Matrix, Self-Laminating Label, 1.9" X .75" X 3.19", 4 Across, White, 2500/pkg



Download spec sheet

Base Data

Local Order Number TAG1-100

Type TAG1

Color White (WH)

Features and Benefits

- Tabtag Dot Matrix labels are specifically made for use in dot matrix printers for fast and easy printing.
- Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.

Color Marking Field White (WH)

Product Description Used with dot matrix printers, HellermannTyton TabTags can be used for virtually any labeling application. Unless noted, TabTags are mounted on pinfed, fan-folded sheets for use with computers, word processors, or typewriters. Manufactured in a wide range of standard sizes and materials, the dot matrix printable TabTags can meet a wide variety of labeling requirements.

Mounting method Identification ETIM Pasting / Stick

Local Order Number 2 595-01100

Short Description Dot Matrix, Self-Laminating Label, 1.9" X .75" X 3.19", 4 Across, White, 2500/pkg

Product Dimensions

Length L (Imperial) 3.19 "

Length L (Metric) 81.0 mm

Self adhesive (Yes/No) Yes

Variant Adhesive label

Width W (Imperial) 1.9 "

Width W (Metric) 48.0 mm

Height H (Imperial) 0.75 "

Height H (Metric) 19.05 mm

Height H2 (Imperial) 3.19 "

Height H2 (Metric) 81.0 mm

Height of printable area (metric) 19.00 mm

Bundle Diameter Min. (Imperial) 0.389 "

Bundle Diameter Min. (Metric) 9.90 mm

Bundle Diameter Max. (Imperial) 0.77 "

Bundle Diameter Max. (Metric) 19.70 mm

Outside Diameter Min. (Imperial) 0.389 "

Outside Diameter Min. (Metric) 9.9 mm

Outside Diameter Max. (Imperial) 0.77 "

Outside Diameter Max. (Metric) 19.70 mm

Horizontal Repeat HR (metric)	50.80 mm
Horizontal Repeat HR (imperial)	2.000 "
Print Method	Dot-Matrix
Thickness T (Metric)	75.0 µm
Vertical Repeat VR (metric)	88.90 mm
Vertical Repeat VR (imperial)	3.5 "
Width of Liner WL (imperial)	9.5 "
Width of Liner WL (metric)	241.30 mm

Logistics and Packaging

Quantity Per	pack
Package Quantity	2500
Package Quantity (Metric)	2500
Carton Quantity	2500 Pieces
Labels per Column	4
Labels per Row	4
Labels per Sheet	12
Weight (Metric)	0.8 kg

Material and Specifications

Material	Type 100, Vinyl (PVC), white (WH), self laminating
Material Shortcut	100
Adhesive	Acrylic
Adhesive Shortcut	Acrylic
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-51°F to +200°F (-46°C to +93°C)
ROHS Compliant	Yes
Certification/Specification	UL-Recognized