


TAG26L-105

Article Number: 594-26105

Laser Tag Self-Laminating Label, .50" X .315" X .75", 156 Per Sheet, Polyester, White, 5000/pkg



Base Data

Local Order Number	TAG26L-105
Type	TAG26L
Color	White (WH)
Features and Benefits	• LaserTags are sheet fed for easy loading and fast printing. • LaserTags are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing. • LaserTags are printable using toner for long term UV exposure. • LaserTags come in a variety of label sizes and types to fit most applications.
Color Marking Field	White (WH)
Product Description	LaserTags are durable, laser printable labels for applications requiring clear, crisp legibility. The labels are supplied on 8.5" X 11" sheets and are printable using HellermannTyton Tagprint Pro software and a standard laser printer. Specially designed adhesives and materials are used for the LaserTags, ensuring that the labels will not curl, change color, or jam standard laser printers.
Short Description	Laser Tag Self-Laminating Label, .50" X .315" X .75", 156 Per Sheet, Polyester, White, 5000/pkg

Product Dimensions

Length L (Imperial)	0.75 "
Length L (Metric)	19.05 mm
Width W (Imperial)	0.50 "
Width W (Metric)	12.7 mm
Height H (Imperial)	0.375 "
Height H (Metric)	9.52 mm
Height H2 (Imperial)	0.75 "
Height H2 (Metric)	19.05 mm
Height of printable area (imperial)	0.375 "
Height of printable area (metric)	9.50 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.50 mm
Bundle Diameter Max. (Imperial)	0.118 "
Bundle Diameter Max. (Metric)	3.00 mm
Outside Diameter Min. (Imperial)	0.059 "
Outside Diameter Min. (Metric)	1.5 mm
Outside Diameter Max. (Imperial)	0.118 "
Outside Diameter Max. (Metric)	3.00 mm
Horizontal Repeat HR (imperial)	.500 "

Horizontal Repeat HR (metric)	12.70 mm
Print Method	Laser
Thickness T (Metric)	35.0 µm
Vertical Repeat VR (metric)	19.00 mm
Vertical Repeat VR (imperial)	0.75 "
Width of Liner WL (metric)	215.00 mm
Width of Liner WL (imperial)	8.5 "

Logistics and Packaging

Quantity Per	pack
Package Quantity	5000
Package Quantity (Metric)	5000
Carton Quantity	5000
Labels per Column	16
Labels per Row	16
Labels per Sheet	256
Weight (Metric)	0.069 kg

Material and Specifications

Material	Type 105, Polyester (PET), white (WH)
Material Shortcut	105
Adhesive	Acrylic
Adhesive Shortcut	Acrylic
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
ROHS Compliant	Yes