

TAG27-400

Article Number: 595-27400

Dot Matrix Label, 1.5" X .75", 4 Across, Metalized Polyester, Silver, 5000/pkg



 Download spec sheet

Base Data

Local Order Number	TAG27-400
Type	TAG27
Color	White (WH)
Features and Benefits	• Tabtag Dot Matrix labels are specifically made for use in dot matrix printers for fast and easy printing. • Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.
Product Description	Used with dot matrix printers, HellermannTyton TabTags can be used for virtually any labeling application. Unless noted, TabTags are mounted on pinfed, fan-folded sheets for use with computers, word processors, or typewriters. Manufactured in a wide range of standard sizes and materials, the dot matrix printable TabTags can meet a wide variety of labeling requirements.
Short Description	Dot Matrix Label, 1.5" X .75", 4 Across, Metalized Polyester, Silver, 5000/pkg

Product Dimensions

Length L (Imperial)	0.75 "
Length L (Metric)	19.0 mm
Width W (Imperial)	1.5 "
Width W (Metric)	38.1 mm
Height H (Imperial)	0.75 "
Height H (Metric)	19.05 mm
Height of printable area (metric)	19.00 mm
Horizontal Repeat HR (imperial)	1.700 "
Horizontal Repeat HR (metric)	43.18 mm
Print Method	Dot-Matrix
Vertical Repeat VR (metric)	25.40 mm
Vertical Repeat VR (imperial)	1.0 "
Width of Liner WL (metric)	193.70 mm
Width of Liner WL (imperial)	7.625 "

Logistics and Packaging

Quantity Per	pack
Package Quantity	5000
Package Quantity (Metric)	5000
Carton Quantity	5000
Labels per Row	4
Weight (Metric)	0.27 kg

Material and Specifications

Material	Type 400, Polyester, white (WH)
Material Shortcut	400
Adhesive Shortcut	Acrylic
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
ROHS Compliant	Yes
Certification/Specification	UL-Recognized