

TAG5J-994

Article Number: 593-05994

Ink Jet Self-Laminating Label, .80" X .50" X 1.625", 40 Per Sheet, Polyester, White, 1000/pkg



 Download drawing

 Download spec sheet

Base Data

Local Order Number	TAG5J-994
Type	TAG5J
Color	White (WH)
Features and Benefits	• HellermannTyton Ink Jet labels are sheet fed for easy loading and fast printing. • Ink Jet labels are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing. • Ink Jet labels are printable using toner for long term UV exposure. • Ink Jet labels come in a variety of label sizes and types to fit most applications.
Color Marking Field	White (WH)
Product Description	Ink Jet labels are durable, ink jet printable markers for applications requiring clear, crisp legibility. The labels are supplied on sheets and are printable using HellermannTyton Tagprint Pro software and a standard ink jet printer. Specially designed adhesives and topcoats accept the ink allowing for easy color printing for specific applications that require colors.
Short Description	Ink Jet Self-Laminating Label, .80" X .50" X 1.625", 40 Per Sheet, Polyester, White, 1000/pkg

Product Dimensions

Length L (Imperial)	1.43 "
Length L (Metric)	36.32 mm
Width W (Imperial)	0.80 "
Width W (Metric)	20.3 mm
Height H (Imperial)	0.50 "
Height H (Metric)	12.7 mm
Height H2 (Imperial)	1.43 "
Height H2 (Metric)	36.5 mm
Height of printable area (imperial)	0.50 "
Height of printable area (metric)	12.70 mm
Bundle Diameter Min. (Imperial)	0.149 "
Bundle Diameter Min. (Metric)	3.80 mm
Bundle Diameter Max. (Imperial)	0.32 "
Bundle Diameter Max. (Metric)	8.00 mm
Outside Diameter Min. (Imperial)	0.15 "
Outside Diameter Min. (Metric)	3.8 mm
Outside Diameter Max. (Imperial)	0.315 "
Outside Diameter Max. (Metric)	8.00 mm
Horizontal Repeat HR (imperial)	.800 "

Horizontal Repeat HR (metric)	20.30 mm
Print Method	Inkjet
Thickness T (Metric)	35.0 µm
Vertical Repeat VR (imperial)	1.43 "
Vertical Repeat VR (metric)	36.32 mm
Width of Liner WL (metric)	215.00 mm
Width of Liner WL (imperial)	8.5 "

Logistics and Packaging

Quantity Per	pack
Package Quantity	1000
Package Quantity (Metric)	1000
Carton Quantity	1000
Labels per Column	4
Labels per Row	10
Labels per Sheet	40

Material and Specifications

Material	Type 994, Polyetylenterephthalat (PET)
Material Shortcut	994
Adhesive Shortcut	Acrylic
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
ROHS Compliant	Yes