

AXIS Camera Station S9001 Desktop Terminal

Effective surveillance for server installations



- AXIS Camera Station S9001 Desktop Terminal is an easy-to-install terminal for use with AXIS S1032 or AXIS S1048 recording servers for high-definition surveillance. The terminal is pre-loaded with an AXIS Camera Station client and pre-configured to minimize installation
- AXIS S9001 complements AXIS S1032 or AXIS S1048 recorders for quick setup of a surveillance workstation.

time.

- AXIS S9001 is pre-loaded with an AXIS Camera Station client and Windows operating system.
- Hardware components such as hard disk, graphic card and CPUs, as well as storage capacity are opti-
- mized to meet the demands for reliable high-definition surveillance.
- To further safeguard system uptime, the product includes three years of hardware and software support.
- AXIS S9001 supports multiple monitors for optimal system overview. A keyboard and computer mouse are included.

- > Ease of installation
- > AXIS Camera Station client included
- > Optimized hardware
- > High-definition surveillance
- > Extensive support



Technical Specifications - AXIS Camera Station S9001 Desktop Terminal

Network Video Recorder - Terminal

Model	AXIS Camera Station S9001 Desktop Terminal Version: 1
Required recorders	AXIS S1032 or AXIS S1048
Processor	Intel i5-4570S 2.90 GHz
Memory	4 GB (4096 MB) Memory type: DDR3-SDRAM PC3-12800 (800 MHz) - [DDR3-1600]
Storage	500 GB, 7200rpm HDD with 64 MB cache and SATA 6Gb/s interface
Graphic card	AMD Radeon R5 A240 1 GB DDR3
Optical Disk Drive	OEM DVD-RW
Network Card	Integrated Intel® I217LM Ethernet LAN 10/100/1000 Mbit
System Performance Specification	
Live Video streams	Qualified for resolutions up to 5 Mpixel up to 15 fps at compression level 30.

General	
Compatible Products	Axis network cameras and encoders including HD, Standard resolution, High resolution, Pan Tilt Zoom and thermal cameras with firmware 4.30 or later
Power	Max: 365 W, 100 VAC to 240 VAC
Connectors	6 x USB 2.0, 4 x USB 3.0, 3 x Display Port, 1 x VGA, 1 x Dual link DVI-I, Network connector, Line-in/out connectors, Computer mouse and keyboard connectors
Number of monitors	Max 2
Operating conditions	5 °C to 35 °C (41 °F to 95 °F)
Dimensions	360 x 175 x 417 mm (14.17 x 6.89 x 16.42 in)
Weight	8 kg (17.64 lb)
Approvals	EN/IEC/UL 60950-1, CSA C22.2 No. 60950-1-07, EN 62311, EN 55022, CISPR 22, EN 55024, CISPR 24, EN/IEC 61000-3-2, EN/IEC 61000-3-3, EN/IEC 62623, EN 50581, EN 300 328, EN 301 893, EN 301 489-1, EN 301 489-17, EN 62311
Accessories	
Included accessories	Installation guide, Keyboard (International/US), Computer mouse, Power cable
System accessories	AXIS T8310 Video Surveillance Control Board, AXIS P8221 I/O Audio Module, AXIS A1001 Network Door Controller
Hardware warranty	3-years included

AXIS Camera Station - Video Management Software client

Software	Axis Camera Station 4.x
Languages	All major languages
Video	
Audio	Two-way audio streaming, AAC, G.711, G.726 compression
Video compression	H.264 (MPEG-4 Part 10/AVC), Motion JPEG
Live view	
Map function	Yes
PTZ Control	Yes
Playback	
Smart Search for recordings	Yes
Playback	Up to 64x or frame by frame Up to 25 cameras synchronized playback
Export	Manual and scheduled export, Single images in JPEG format, Video in ASF format, Digital signature on exported recordings, Standalone player

Triggers and events		
Event triggers	Events triggered by video motion detection, Active Tampering Alarm, AXIS Cross Line Detection, External I/O, Action button, System triggers and device event triggers	
Scheduled recording	Schedule per camera for continuous recording or customization of weekday and weekend recordings	
Alarm manager	Yes	
Microsoft Active Directory support	Yes, multiple user access levels with password protection using local or Windows domain users (Active directory)	

More information is available at: www.axis.com/products/cam_station_software

System setup with AXIS S1032 or AXIS S1048 and AXIS S9001



