

Compact All-In-One NVR Appliance

The CIRRUS CR5-TW2 compact video server (NVR) has been designed for performance and peace of mind. Offering recording capacity up to 12TB, the CR5-TW2 offers key features such Quick Setup Wizard, high performance INTEL processor, dedicated SSD boot drive (OS) and dual Gigabit Ethernet.



Features

- Intel® Core i3, i5 and i7 Series Processors
- Up to 12 TB Internal Storage
- Designed for 24/7 Video Recording
- Available Dedicated SSD Boot Drive
- Low Noise Compact Design
- Pre-loaded VMS Software

Base Specifications

Processor	Intel® Core i3-4170 (CR53) Intel® Core i5-4690S (CR55) Intel® Core i7-4790S (CR57)
Memory	4GB DDR3
Operating System	Windows Embedded 7
Drive Bays	2 x 3.5" (fixed)
Drive Capacities	1TB, 2TB, 3TB, 4TB, 6TB
Drive Interface	SATA
Boot Drive (OS)	Optional 128GB SSD SATA3
Video Outputs	DVI, VGA
Max. Resolution	1920 x 1200
Power Supply	180W 100-240Vac 60-50Hz
Networking	2 x GbE LAN
Accessories	AC Power Cord
Form Factor	Compact Tower
Dimensions	8.69" (W) x 8.9" (H) x 12.8" (D)
Operating Temp.	0°C - 60°C (32°F - 140°F)
Warranty	3 Years
Compliance	CE, FCC

Available Options

Up to 16GB Memory	5 Year Warranty Upgrade
Internal DVD-RW	CPU Upgrade (i5, i7)
1GB Graphics Card	

Built tough, built to last.

Available solid state boot drive, internal realtime hardware and software watchdogs and fully recoverable operating system image extends the reliability of your critical installations. The CIRRUS line of IP recording appliances also uses video surveillance hard drives to ensure optimal performance and high reliability for your video recording.

Quick Setup Wizard

The CR5-TW2 is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which VMS software solution to deploy on your NVR appliance.

