

Compact All-In-One NVR Client Workstation



Quick Setup Wizard

The SKYVIEW PRO is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which client software to deploy on your workstation.



Genetec

AVIGILON
THE BEST EVIDENCE™

exacq
Technologies

milestone

AXIS
COMMUNICATIONS

MIRASYS

arteco

IONODES

Features

- Dual Display Support
- 4K Ultra HD Resolution
- Low Noise Compact Design
- Up to 2TB of Internal Storage
- Web Based Administrative Interface
- Rack Mounting Option
- Windows Embedded Standard 7

Standard / Integrated Interfaces

Network	2 x 10/100/1000 Base-T Ethernet port(s) RJ45
USB	2 x USB 2.0 (Mouse, Keyboard, Expansion) 4 x USB 3.0
Display Outputs	VGA, HDMI, DisplayPort (Dual Display Capable) 4K Resolution Support (4096 x 2160) <i>*DisplayPort to DVI Cable Included</i>
Audio	Line Out, Mic In, Speaker, DMIC
Other	1 x COM Port RS-232 1 x DVD-RW

System

Operating System	Windows Embedded Standard 7
CPU / Memory	Intel® Core™ i7-4790T (3.9 GHz) Up to 16GB DDR3 memory
HW Watchdog	Auto-boot, OS supervision, temperature monitoring, software monitoring
Boot Drive	SSD: 128GB (default) or 256GB SATA: 500GB, 1TB or 2TB

Software

Auto-Discovery	Bonjour protocol support
Web Interface	Web GUI for remote config. / maintenance

Mechanical / Environmental

Dimensions	11.8" (W) x 2.6" (H) x 10.7" (D)
Input Voltage	DC Input: 12~24VDC @ 120W (included)
Operating Temp.	0C to 60C
Compliance	CE, FCC
Warranty	2 Years Standard (3 year advanced replacement option)