



Tatung 17" BNC/VGA/HDMI Monitor Specification

Model name: TM17

Items	Unit	Specification
Screen size (Diagonal)	inch	17"
Screen aspect ratio		4:3
Pixel Resolution	Pixel	1280 x 1024
Backlight system	-	CCFL
Luminance, white	cd/m ²	300 (center, typical)
Viewing angle (CR>10)	degree	170 R/L , 160 U/D
Contrast Ratio (typical)		800 : 1
Response time	msec	5 (G to G)
Power consumption	watt	40
Power input		AC 120V – 240V
Input/output		VGA DVI via adapter through HDMI (DVI to HDMI adapter is not included) HDMI BNC in Composite Video in BNC out (when monitor is on with input selection at BNC in)
Speaker output	watt	3w + 3 w
VESA mounting holes		75 mm x 75 mm
Dimension – with packaging	inch	17.91 x 5.04 x 16.54
Dimension – without packaging	inch	15.55 x 2.76 x 15.36
Weight	lb	Gross 12.1 Net 8.8
Operating temperature	°C	5 ~ 40
Storage temperature	°C	-20 ~ 55