

Maximum load rating: 75 lbs

SECTION A

CRIMSON AV LLC.
PRODUCT ORDER NUMBER: **RW90**
PHONE: **1-866-668-6888**

Scale=1:1

CRIMSON
AV MOUNTING SOLUTIONS

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CRIMSON AV LLC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CRIMSON AV LLC IS PROHIBITED

Crimson AV LLC.
www.crimsonav.com

TITLE:
RW90

SIZE B
DWG.N.O.
RW90

Dimensions (inches [millimeters]):

- Top view: 7.25" [184.15MM] (overall width), 5.50" [139.70MM] (inner width), 11.76" [298.82MM] (overall height), 2.00" [50.80MM] (height of lower section), 2.88" [73.15MM] (height of upper section), 0.87" [22.10MM] (height of top flange), 1.00" [25.40MM] (width of central hole), 2-? 0.75" [? 19.00MM] (two small holes), 4-3/8" (four mounting holes).
- Side view: 6.58" [167.20MM] (width), 3.82" [97.03MM] (height), 2.47" [62.67MM] (width of base), 90° (angle of base), 135° (angle of side flange), 5.61" [142.48MM] (length of side flange).
- Perspective view: 5.26" [133.53MM] (width), 2.50" [63.50MM] (height), 0.99" [25.09MM] (width of top flange), 6-? 0.44" [? 11.13MM] (six mounting holes).

CRIMSON
AV MOUNTING SOLUTIONS

PRODUCT ORDER NUMBER: **RW90**
PHONE: **1-866-668-6888**

Crimson AV LLC. www.crimsonav.com	
TITLE: RW90	
SIZE B	DWG.N.O. RW90