



Maximum load rating: 100 lbs

MAX:52.1"[1323.34mm]
Min:42.9"[1089.7mm]

Max:45.3"[1150.6mm]
Min:11.8"[299.1mm]

0"~9.2"[233.7mm]

11.01" [279.60mm]
8.00" [203.20mm]

24.59" [624.60mm]
23.70" [602.10mm]
15.85" [402.50mm]

3.94" [100.19mm]

Up&Down

5.32" [135.19mm]

13.04" [330.40mm]

UP 0.5" [12.7mm]

DOWN 0.5" [12.7mm]

IN 0.5" [12.7mm]

OUT 0.5" [12.7mm]

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF CRIMSON AV LLC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF CRIMSON AV LLC IS PROHIBITED



CRIMSON AV LLC.

PRODUCT ORDER NUMBER: **VWC60**
PHONE: 1-866-668-6888

Scale=1:1

Crimson AV LLC.
www.crimsonav.com

TITLE: **VWC60**

SIZE DWG.N.O. **VWC60**