



Male Tab

T&B Catalog Number:

10RC-250T

UPC Number:

78621083934

Status:

Active

Description:

Vinyl-Insulated Male Tab, Length 1.08 Inches, Maximum Insulated .250, Tab Size .250x.032, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Style	Male - 250 Series
Insulation Type	Insulated Vinyl
Terminal Series	RC
Material	Brass
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Tab Size	.250 x .032

Dimension Information

Maximum Insulation (inches)	.250
Stock Thickness	.04
A (inches)	1.08

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	5 lbs. per 1000
Alternate Package Qty	RC2517

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com