

Thin-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

CPO1000-0-6

UPC Number:

78621085178

Status:

Active

Description:

Thin-Wall Heat-Shrinkable Tubing for Cable Range 2/0 - 350 kcmil, Expanded Diameter 1 Inch, Length 6 Inch, 600 Volt, 125 Degrees Celsius, Cross-linked Polyolefin - Non-Lined, Black



Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

General

Style	CPO Series Non-Lined, 6 in. lengths
Color	Black
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

Dimension Information

Minimum Expanded I.D. (inches)	1
Maximum Recovered I.D. (inches)	0.5
Nominal Recovered Wall (inches)	0.035
Cable Range	2/0 - 350 MCM
Standard Length (inches)	6

Specifications

Shrink Temperature	120°C
--------------------	-------

Packaging

T&B Order Multiple	5
T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. per 100

Application Support

MSDS Number	sds-00046-tb2
Specifications	Available on Website
Overview	Available on Website

Notes

Order multiple is standard package.

Custom colors available. Contact Customer Service.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com