

## Thin-Wall Heat-Shrinkable Tubing

**T&B Catalog Number:**

CPO125-0-C

**UPC Number:**

78621083360

**Status:**

Active

**Description:**

Thin-Wall Heat-Shrinkable Tubing for Cable Range 30 - 24 AWG, Expanded Diameter 1/8, Length 100 feet reel, rated for 600 Volt, 125 degrees C, Material: Cross-linked polyolefin - Non-lined, Black

### Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### General

Style	CPO Series Non-Lined
Color	Black
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

### Dimension Information

Length (feet)	100
Minimum Expanded I.D. (inches)	0.125
Maximum Recovered I.D. (inches)	0.062
Nominal Recovered Wall (inches)	0.02
Cable Range	30 - 24 AWG

### Specifications

Shrink Temperature	120°C
--------------------	-------

### Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.75 lbs. Each

### Application Support

Specifications	Available on Website
Overview	Available on Website

### Notes

Order multiple is for 4 ft. sticks is 25 sticks. Order multiple for reels is 1 reel. When ordering standard package, order by package not feet.

UL Recognized File Number E137759 and CSA Certified. Clear material not UL Recognized.

Larger diameters available upon special request; consult Customer Service.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)