

CPO750-0-C



Shrink-Kon®

CPO Series Thin-Wall Heat-Shrinkable
Tubing

General

Type:	Thin-Wall Heat-Shrinkable Tubing
Shrink Ratio:	2:1
T&B UPC:	78621083642
T&B Status:	M
Colour:	Black
Material:	Flame-retardant, cross-linked polyolefin

Dimension Information

Cable Range:	4/0 - #2 AWG
Continuous Operating Temperature:	-55°C to 135°C
Shrink Temperature:	120°C
Length:	100 ft.