



**Pipe Straps, Pipe Clamps & Hangers (Series 700)**

**T&B Catalog Number:**

CPC400

**UPC Number:**

61601310716

**Status:**

Active

**Description:**

Clamp, One-Piece Cable and Pipe, EMT and Rigid Conduit Trade Size 4 Inches, Cable Outer Diameter Range 4.126-4.626 Inches, Steel

**Features**

One-piece, heavy-duty construction ready to install right out of the box, no need to break apart and re-assemble, no screws or bolts to drop.

Heavy-duty 5/16 in. hex bolt with multi-driver head, Robertson square, Phillips cross-recess and slot, provides a full range of installation options.

Reconfigure wiring without complete disassembly. Remove cables easily without disturbing neighboring clamps.

Parallel hook design keeps conduits and cable square with strut.

Works with all depths of strut - 13/16 in. to 3 1/4 in.

**Application**

Attaches a full range of EMT, Rigid conduit and cable to strut channels.

**General**

Trade Size (inches)	4
Material	Steel
Finish	SilverGalv
Static Load Limit (lb)	350
Safety Factor	4

**Dimension Information**

Cable O.D. Range (inches)	4.126-4.626
---------------------------	-------------

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	0.47 lbs. per 100

**Application Support**

Product Brochure-Cobra Cable & Pipe Clamp	Available on Website
---	----------------------

**Notes**

Safety factor 4:1 (safety factor is ratio of ultimate load to the design load)

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)