



## Thin-Wall Heat-Shrinkable Tubing

**T&B Catalog Number:**

HS-KIT

**UPC Number:**

78621093898

**Status:**

Active

**Description:**

Thin-Wall Heat Shrinkable Tubing Assortment Precut in 6 Inch Lengths, Black, (32)-Diameter 3/16 Inch, (20)-Diameter 1/4 Inch, (8)-Diameter 3/8 Inch, (6)-Diameter 1/2 Inch, (4)-Diameter - 3/4 Inch, (4)-Diameter - 1 Inch Includes Plastic Storage Case

### Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### General

Style	CPO Series Non-Lined - Kit
Color	Black
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

### Specifications

Shrink Temperature	120°C
--------------------	-------

### Packaging

T&B Order Multiple	1
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.3 lbs. per 100

### Application Support

Specifications	Available on Website
Overview	Available on Website

### Notes

UL Recognized File Number E137759 and CSA Certified. Clear material not UL Recognized.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com