



Push Mount
T&B Catalog Number:

L-7-50PM-0-D

UPC Number:

72849412452

Status:

Active

Description:

Push Mount Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21, Length of 208mm (8.19 Inches), Width of 4.8mm (0.189 Inches), Thickness of 1.19mm (0.047 Inches), Panel Mounting Hole Size of 6.35mm (0.25 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

General

Material	Nylon 6.6 Weather Resistant
Color	Black
Mounting Hole Size	1/4

Dimension Information

Nominal Length (inches)	8
Length (inches)	8.2
Width (inches)	0.187
Max. Wire Bundle Diameter (inches)	1 3/4
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	3.13 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000315
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com