



## Project: QUALITY CABLE QUALITY

**3/4 x 3/4 Mount**  
**T&B Catalog Number:**

MPNY-750-0-C

**UPC Number:**

72849409535

**Status:**

Active

**Description:**

Cable Tie Mounting Base, Black Nylon 6.6 for Temperatures up to 70 Degrees Celsius (158 F), Length of 19.05mm (0.75 Inches), Width of 19.05mm (0.75 Inches), Height of 5.21mm (0.205 Inches), Synthetic Rubber Adhesive Mounting Method, 100 Pack

### General

Material	Nylon 6.6
Color	Black
Mounting Method	Adhesive
For Cable Ties	Up to 30 lbs.

### Dimension Information

Length (inches)	.750
Width (inches)	.750
Maximum Height (inches)	.205
Slot Height (inches)	.05
Slot Width (inches)	.140

### Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

### Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	10000
Package Type	Regular
T&B Sold in UOM	Each
T&B Weight Per UOM	1.88 lbs. per 1000

### Application Support

T&B Sales Drawings	wsd-001485
Material Selection Guide	Available on Website

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

E49405

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)