



Project: QUALITY CABLE QUALITY

1 1/8 x 1 1/8 Mount

T&B Catalog Number:

MPNY-1000-0-C

UPC Number:

72849410099

Status:

Active

Description:

Cable Tie Mounting Base, UV Black Nylon 6.6 for Temperatures up to 70 Degrees Celsius (158 F), Length of 28.58mm (1.125 Inches), Width of 28.58mm (1.125 Inches), Height of 5.08mm (0.20 Inches), Synthetic Rubber Mounting Method, 100 Pack

General

Material	Nylon 6.6
Color	Black
Mounting Method	Adhesive
For Cable Ties	Up to 50 lbs.

Dimension Information

Length (inches)	1.125
Width (inches)	1.125
Maximum Height (inches)	.215
Slot Height (inches)	.070
Slot Width (inches)	.203

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	3.75 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-001486
Material Selection Guide	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E49405

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com