



Intermediate T&B Catalog Number:

L-8-40-9-M

UPC Number:

72849491850

Status:

Active

Description:

Intermediate Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 215mm (8.46 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

General

Material	Nylon 6.6
Color	Natural

Dimension Information

Nominal Length (inches)	8
Length (inches)	8.5
Width (inches)	0.130
Max. Wire Bundle Diameter (inches)	2
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000221
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com