

**Standard****T&B Catalog Number:**

L-11-50-9-D

UPC Number:

72849491130

Status:

Active

Description:

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 295.66mm (11.64 Inches), Width of 4.73mm (0.186 Inches), Thickness of 1.35mm (0.053 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Military Specified (MIL-SPEC MS3367-7-9), Bulk Pack

General

Material	Nylon 6.6
Color	Natural

Dimension Information

Nominal Length (inches)	11
Length (inches)	11.1
Width (inches)	0.187
Max. Wire Bundle Diameter (inches)	3
Min. Wire Bundle Diameter (inches)	1/16

Specifications

Military Standard Part No.	MS3367-7-9
Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

Packaging

T&B Order Multiple	5000
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	4.38 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000222
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com