

**Minature****T&B Catalog Number:**

L-6-18-0-C

UPC Number:

72849493365

Status:

Active

Description:

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 162mm (6.38 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	6
Length (inches)	6.4
Width (inches)	0.100
Max. Wire Bundle Diameter (inches)	1 3/8
Min. Wire Bundle Diameter (inches)	1 1/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG50, QC-100, L-200, L-400-C
-------------------	-------------------------------

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	20000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1.29 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000218
Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com