



FiberChek™ Probe Microscope

Specifications

Parameter		
Dimensions (H x W x D)		218 x 50 x 131 mm (8.6 x 2.0 x 5.2 in)
Weight		272 g (9.5 oz)
Display		128 x 128 x 1.5 in OLED touch screen
Connector		USB 2.0 (Micro-B)
Power source		Internal LiON battery, USB power
Run time		6 hr
Charge time		2 hr (2 A max power source) 8 hr (500 mA max power source)
Field-of-view values (µm)	High Magnification	Horizontal: 740 µm Vertical: 550 µm
	Low Magnification	Horizontal: 370 µm Vertical: 275 µm
Live image		640 x 480
Power supply		12 V, 2 A with interchangeable wall plug for EU, UK, US, and AU
Camera sensor		2560 x 1920, 1/2.5 in CMOS, 5 megapixel
Particle size detection		<1 µm
Built-In LCD resolution (in pixels)		Live Image: 320 x 240
Particle size detection		<0.5 µm
Light source		Blue LED, 100,000+ hr life
Lighting technique		Coax
Certification		CE, EN/IEC 61326

* With standard tip (FBPP-U25M), no dust cap.

Ordering Information

Description	Part Number
FiberChek probe, case, FBPT-U25M, tip case	FIT-FC-KIT1
Kit: FiberChek probe, case, FBPT-LC, FBPT-SC, FBPT-U12M, FBPT-U25M, tip case	FIT-FC-KIT2
Kit: FiberChek probe, case, FBPT-LC, FBPT-SC, FBPT-SC-APC, FBPT-U12M, FBPT-U25M, FBPT-U25MA, tip case	FIT-FC-KIT3
FiberChek case	FCPP-SCASE3
Locking MicroUSB cable	FBPP-DPAC7
OTG cable	FBPP-DPAC8
FiberChek holster	FCPP-CHP1

Visit www.viavisolutions.com for more information, vendor endorsements, and product videos.

Contact Us **+1 844 GO VIAVI**
(+1 844 468 4284)

To reach the Viavi office nearest you,
visit viavisolutions.com/contacts.

© 2016 Viavi Solutions Inc.
Product specifications and descriptions in this document are subject to change without notice.
fiberchek-ss-fit-nse-ae
30179721 000 0416