


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. MILLIMETERS ARE SHOWN IN [ ]
2. WILL ACCOMODATE VALVE HANDLES WIDTHS UP TO 1.70"
3. NO LIMIT ON HANDLE LENGTH
4. OPERATING TEMPERATURE -40° F [ -40° C ] TO 215° F [ 120° C ]

CAD FILENAME/LAYERS 100923AC\_DC-C10634/01C

PANDUIT CORP TINLEY PARK, ILLINOIS

PSL-BFV BUTTERFLY VAVLE LOCKOUT CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 (.X) ± .050 (.XXX) ± .010  
 (.XX) ± .020 ANGLES ± 1°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	12-21-10	JHAC	<i>JHAC</i>	ADDED NOTES 2,3, AND 4	6256	R		
1	5-5-08	JHAC		CHANGED DIMENSION FROM 12.25 to 12.00 AND ADDED TOLERANCE OF 0.100 TO 12.00 DIMENSION	5416	R		
0	1-18-08	JHAC		DRAWING RELEASE	5266	R		

DRAWN BY JHAC  
 DATE 1-18-08  
 CHK'D *JHAC*

MAT'L: RED POLYPROPYLENE

SCALE NTS  
 DRAWING NO. C10634  
 DWG SIZE B