




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. OPERATIONAL TEMPERATURE RANGE:
-40°F (-40°C) TO 140°F (60°C)
2. STORAGE TEMPERATURE RANGE:
-40°F (-40°C) TO 250°F (120°C)
3. HOLDS 6 PADLOCKS
4. DIELECTRIC

										CAD FILENAME/LAYERS		100923D0_DC_C10890/00A	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										PSL-NC3 PLASTIC HASP CUSTOMER DRAWING			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XX) ± .05		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY JHAC		SCALE 1 : 2 DRAWING NO. C10890 DWG A SIZE	
										DATE 02/24/11			
										CHK'D M-L			
0	2/24/11	JHAC	<i>[Signature]</i>	DRAWING RELEASE		6289					RED NYLON		
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP			