

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

COVER REMOVED FOR CLARITY

PAN-TY LOOPS
FOR CABLE HOLD-DOWNS
(3 PLACES)

BREAKOUT AREA
(3 PLACES)

KNOCK OUT
MOUNTING HOLES
FOR #6 PAN
HEAD SCREW
(INCLUDED)

3.281
[83.34]

POST FOR TAMPER
RESISTANT SCREW

3.28
[83.3]

.94
[24.0]

4.65
[118.1]

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. BOX INCLUDES:
 - 1- BOX BASE
 - 1- BOX COVER
 - 2- PLT1.5I-M PAN-TY
 - 1- LABEL/ LABEL COVER
 - 2- MOUNTING SCREW
 - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
 - 2- STRIP OF 1.00" X .75" FOAM TAPE FOR MOUNTING
 - 1- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
5. BASE HAS TWO POCKETS FOR OPTIONAL MAGNET (CSBM-X)
6. BREAKOUTS DESIGNED TO ACCEPT LD3/LDPH3 AND LD5/LDPH5 RACEWAY.
7. BASE MATERIAL THICKNESS= .090[2.29].

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

PART NUMBER

CBXS4**-AY

TITLE

MINI-COM 4 POSITION SHUTTERED SURFACE MOUNT BOX

CUSTOMER DRAWING

ITEM REVISION NAME

M02479EU/02

DATASET FILE NAME

M02479EU_DC127/02A


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±

.XXX ± .010 [.3]

.XX ± .03 [.8]

ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

BOX: ABS
DOORS: PC

DRAWING NUMBER:

02479-127

DRAWN BY

JSP

DATE

12-27-06

CHK

MJD

SCALE

NONE

SHT 1 OF 1

SIZE

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	3/19/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-127
R	12-27-06	JSP	MJD	MJD	RELEASED TO PRODUCTION	02479-127