THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CFPL10S-2GY	2.15 LB/10 PCS (975.2g/10 PCS)



NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. PART INCLUDES:
   1- FACEPLATE
   4- #6-32 X 1" MOUNTING SCREWS
   2- LABEL
   2- LABEL COVER



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	4/15/14	JSP	REFR	MMR	B. REVISED DRAWING TITLE BLOCK.	02479-228
1	7-30-07	JSP	JCO	JCO	A. FACEPLATE MATERIAL WAS JSUT STAINLESS STEEL	02479-228
R	3-25-06	JSP	MJD	MJD	RELEASED TO PRODUCTION	02479-228

PART NUMBER: CFPL10S-2GY

TITLE: MINI-COM 10 POSITION STAINLESS STEEL DOUBLE GANG FACEPLATE WITH LABEL/COVER

CUSTOMER DRAWING

ITEM REVISION NAME: M02479IR/03

DATASET FILE NAME: M02479IR_DC228/03A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [.3]
.XX ± .03[.8] ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: FACEPLATE- 304 S.S.
BACKING- ABS

DRAWING NUMBER: 02479-228

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JCO	3-25-06	MJD	NONE		A

D10100DA/14