


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DESCRIPTION	WEIGHT
CJ64XX**Y	6 POSITION, 4 WIRE TERMINATION CAP	1.62 lb/100 PCS. [738 g/100 PCS.]
CJ66XX**Y	6 POSITION, 6 WIRE TERMINATION CAP	1.62 lb/100 PCS. [738 g/100 PCS.]
CJ66UXX**Y	6 POSITION, 6 WIRE MODULAR JACK TERMINATION CAP IS COLOR CODED FOR USOC WIRING SCHEME	1.62 lb/100 PCS. [738 g/100 PCS.]

**NOTE:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. MATERIAL:
JACK HOUSING - ABS
NOMINAL WALL THICKNESS .078[2.0].
TERMINATION CAP - POLYCARBONATE.
3. THIS PART IS DESIGNED FOR USE WITH MINI-COM PLATES AND BOXES.
4. MEETS ALL CATEGORY 3 PERFORMANCE REQUIREMENTS AS DEFINED BY EIA/TIA.
5. DIMENSIONS IN PARENTHESIS ARE IN METRIC.

PART NUMBER	
CJ64XX**Y, CJ66XX**Y, CJ66UXX**Y	
TITLE	
MINI-JACK CATEGORY 3 TWISTED PAIR CONNECTOR	
CUSTOMER DRAWING	
ITEM REVISION NAME	
M02479NJ/00	
DATASET FILE NAME	
M02479NJ_DC349/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.x ± .xxx ± .010 [.3] .xx ± .03 [.8] ANGLES ±	
THIRD ANGLE PROJECTION	
DRAWN BY	
NER	
DATE	
3-25-06	
CHK	
WJC	
SCALE	
NONE	
MATERIAL:	
SEE NOTES	
DRAWING NUMBER:	
02479-349	
REV	
DATE	
BY	
CHK	
APR	
DESCRIPTION	
ECN	
SHT 1 OF 1	
SIZE	
A	