



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART#	DESCRIPTION	WEIGHT*
CJD6X88TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. BLUE WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.58 LB/100 PCS (721g/100 PCS)



- *WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX
- NOTES:
1. BLUE WIRE CAP DESIGNATES AUGMENTED CATEGORY 6 PERFORMANCE.
 2. TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 3. MATERIAL:
MODULE HOUSING - ABS
WIRE CAP - PC
STRAIN RELIEF CLIP - PC
SHUTTER DOOR - PC
 4. ALL TX6 10GIG, 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
 5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ACTUAL SIZE



PART NUMBER		SEE CHART	
TITLE			
TX6A 10GIG SHUTTERED UTP JACK MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01874SI/07	
DATASET FILE NAME		M01874SILDC43/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)			
.xx ± .03 (.8)		ANGLES ±	
		DRAWING NUMBER: 01874-43	
DRAWN BY	DATE	CHK	SCALE
MDJR	9-29-04	EJH	FULL
SHT 1 OF 1			SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	5-22-14	TA	REFR	REFR	REVISED TITLE BLOCK REVISED AND REDRAWN WITH THE LATEST REV INFORMATION	

D10100DA/14

2

1

2

1