

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

A



PART#	COLOR	DESCRIPTION	WEIGHT*
CJS6X88TGY CJS6X88TGRDY CJS6X88TGBUY CJS6X88TGGRY CJS6X88TGVLY CJS6X88TGYLY	BLACK RED BLUE GREEN VIOLET YELLOW	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)

*WEIGHT IS APPROXIMATE

NOTES:

1. BLUE WIRE CAP DESIGNATES CATEGORY 6A PERFORMANCE.
2. MATERIAL:
MODULE HOUSING- ABS
MODULE SHIELD- TIN PLATED PHOS. BRONZE.
WIRE CAP SHIELD- TIN PLATED CARTRIDGE BRASS
WIRE CAP- PC
3. ALL CATEGORY 6A, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.

STRAIN RELIEF CLIP




WIRE CAP SHIELD

B


WIRE CAP

GROUNDING TAB
(SEE NOTE 5)MODULE
SHIELD


MODULE HOUSING




.62
[15.87]



.75
[18.94]



1.50
[38.07]



ACTUAL SIZE

PART NUMBER		CJS6X88TG**Y	
TITLE		TX6A 10GIG SHIELDED JACK MODULE	
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NU/04	
DATASET FILE NAME		M02479NU_DC359/04A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ±		.XXX ± .010 [.3]	
.XX ± .03 [.8]		ANGLES ±	
		THIRD ANGLE PROJECTION	
DRAWN BY		DATE	
AFW		3-11-06	
CHK		NGM	
SCALE		FULL	
DRAWING NUMBER:		02479-359	
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	10-26-15	BJN	WFMI	FMS	B. UPDATED MODEL TO 12M330AR/06 TO ADD WIRE CAP SHIELD	02479-359
3	5-21-14	MDJR	REFR	EJH	A. ADDED PART NUMBERS FOR COLORS RED, BLUE, GREEN, VIOLET AND YELLOW. PREVIOUS REVISIONS OMITTED FOR CLARITY.	02479-359