


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TABLE 1	
PLUG PACK	CUSTOMER DRAWING#
6-POSITION	02802-19
8-POSITION	02802-25
12-POSITION	02802-26
RECESSED	03073-06

NOTES:

1. HARNESS IS AVAILABLE IN PLUG PACK/CASSETTE OR LOOSE JACK AND PLUG/CASSETTE OR LOOSE JACK CONFIGURATIONS. SEE CHART ON SHEET 4 FOR PRODUCT OPTIONS.
2. PATCH CORDS ARE BUNDLED USING HLS VELCRO STRAPS AT 12" [305mm] SPACING.
3. EACH PATCH CORD IS SEQUENTIALLY NUMBERED AT BOTH ENDS WITH PORT I.D. LABELS.
4. PATCH CORD I.D. LABELS CONTAIN PATCH CORD PERFORMANCE, PART#, LENGTH (L), AND QC#.
5. PLUG PACK I.D. LABELS AND PLFIMA MARKER TIES ARE INCLUDED FOR CUSTOMER APPLIED SWITCH AND PORT IDENTIFICATION. FOR PRINTABLE LABEL OPTIONS, REFER TO PANDUIT C125X030FJJ, C125X030YPT AND C125X030FJC.
6. CORDS ARE 100% PERFORMANCE TESTED.
7. SEE CATALOG FOR OPTIONAL REMOVAL TOOL (QPRT) AND LOCK-IN DEVICE (QPPLD*)



QPC*****
6-CABLE ASSEMBLY
PLUG PACK TO
CASSETTE SHOWN

PART NUMBER	PRODUCT SPEC/PKG SPEC
QPC*****;QPJ*****	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE
QUICKNET SWITCH PORT HARNESS
 CUSTOMER DRAWING

ITEM REVISION NAME
M02802ES/00

DATASET FILE NAME
M02802ES_DC43/00B

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ± .1 [2.54] .xxx ± .005 [.127]
 .xx ± .01 [.25] ANGLES ± 5 °

THIRD ANGLE PROJECTION

MATERIAL:


DRAWING NUMBER:
02802-43

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	1/28/14	BJN	WFMI	TMBA	B. CORRECTED DATE ON TITLE BLOCK ON SH2 A. CORRECTED TITLE BLOCK ON SH3 TO READ CUSTOMER DWG	02802-43
R	12-19-13	BJN	WFMI	TMBA	RELEASED TO PRODUCTION	02802-43


DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 4	SIZE
BJN	12-19-13	WFMI	NONE		A

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PLUG PACK END



CASSETTE END

QPC*****
12-CABLE ASSEMBLY WITH
CASSETTES (SD CASSETTE SHOWN
FOR 28AWG CABLE ONLY)

PART NUMBER	PRODUCT SPEC/PKG SPEC
QPC***** ; QPJ*****	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE	QUICKNET SWITCH PORT HARNESS
	CUSTOMER DRAWING

ITEM REVISION NAME	M02802ES/00
DATASET FILE NAME	M02802ES_DC43/00B


UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)	MATERIAL:
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °	
THIRD ANGLE PROJECTION	DRAWING NUMBER: 02802-43

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	1-28-14	BJN	WFMI	TMBA	SEE SHEET 1 FOR REVISION HISTORY	02802-43
R	12-19-13	BJN	WFMI	TMBA	SEE SHEET 1 FOR REVISION HISTORY	02802-43

DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 4	SIZE
BJN	12-19-13	WFMI	NONE		A

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



QPJ*****
 6-CABLE ASSEMBLY
 PLUG PACK TO
 LOOSE JACKS SHOWN

PART NUMBER	PRODUCT SPEC/PKG SPEC
QPC***** ; QPJ*****	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE	QUICKNET SWITCH PORT HARNESS
ITEM REVISION NAME	CUSTOMER DRAWING
DATASET FILE NAME	M02802ES/00
	M02802ES_DC43/00B

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °	

MATERIAL:	DRAWING NUMBER:
	02802-43
THIRD ANGLE PROJECTION	

1	1-28-14	BJN	WFMI	TMBA	SEE SHEET 1 FOR REVISION HISTORY	02802-43
R	12-19-13	BJN	WFMI	TMBA	SEE SHEET 1 FOR REVISION HISTORY	02802-43


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 3 OF 4	SIZE
							BJN	12-19-13	WFMI	NONE		A

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

QUICKNET SWITCH PORT HARNESS MATRIX

QPC	A	C	B	A	B	B	03
QUICKNET SWITCH HARNESS TYPE	PERFORMANCE LEVEL	FLAME/SMOKE RATING	CABLE COLOR	PLUG PACK CONFIGURATION	PLUG PACK COLOR	JACK COLOR	PATCH CORD ASSEMBLY LENGTH IN FT/M
QPC QUICKNET PLUG TO CASSETTE HARNESS	A - CAT 6A (10Gig) UTP	C - CM	B - BLUE	A - 6 PACK	B - BLUE	B - BLUE	05=5 FEET
	C - CAT 6 UTP	L - LOW SMOKE ZERO HALOGEN (LSZH)	W - WHITE	B - 12 PACK	W - WHITE	W - WHITE	07=7 FEET
QPJ QUICKNET PLUG TO LOOSE JACK HARNESS	D - CAT 5e UTP	D - DUAL RATING (MEETS BOTH CM AND LSZH)	G - INTERNATIONAL GRAY (FOR STP ONLY)	D - 8 PACK	R - RED	R - RED	10=10 FEET
	E - CAT 6A (10Gig)/ CAT 6 STP		N - GREEN	R - RECESSED 6 PACK	L - BLACK	L - BLACK (ALL STP JACKS)	14=14 FEET
	S - CAT 6 SD UTP (2BAWG) USE SD CASSETTE		R - RED	P - TWO 6 PACKS ON 12 CABLE HARNESS	S - SILVER (RECESSED ONLY)	I - INTERNATIONAL GRAY	20=20 FEET
	T - CAT 5e SD UTP (2BAWG) USE SD CASSETTE		Y - YELLOW	S - TWO RECESSED 6 PACKS ON 12 CABLE HARNESS	X - NO PLUG PACK		2M=2 METERS
	X - CAT 6A UTP MATRIX SD		O - ORANGE	6 - 6 CABLES (IF NO PLUG PACK)		G - GREEN	3M=3 METERS
	Z - CAT 6A UTP MATRIX		V - VIOLET	8 - 8 CABLES (IF NO PLUG PACK)		Y - YELLOW	4M=4 METERS
			L - BLACK	W - 12 CABLES (IF NO PLUG PACK)		O - ORANGE	5M=5 METERS
	A - GRAY (FOR UTP SD ONLY)			V - VIOLET	6M=6 METERS		
						#=# FEET	
						#M=# METERS	

PART NUMBER QPC***** ; QPJ*****		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE QUICKNET SWITCH PORT HARNESS CUSTOMER DRAWING			
ITEM REVISION NAME M02802ES/00		PANDUIT	
DATASET FILE NAME M02802ES_DC43/00B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER: 02802 - 43	
 THIRD ANGLE PROJECTION			
DRAWN BY BJN	DATE 12-19-13	CHK WFMI	SCALE NONE
REV		SHT 4 OF 4	
DATE		SIZE A	
BY			
CHK			
APR			
DESCRIPTION		ECN	

D10100DA/14