


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CHART FOR PRODUCT OPTIONS.
2. PATCH CORDS ARE HELD TOGETHER USING HLS TAK-TY STRAPS AT 12" (305mm) SPACING.
3. EACH PATCH CORD IS SEQUENTIALLY NUMBERED AT BOTH ENDS WITH PORT ID LABELS.
4. PATCH CORD ID LABELS CONTAIN PATCH CORD PERFORMANCE, PART#, LENGTH(L), AND QC#.
5. ONE SET OF PLUG PACK ID LABELS AND ONE PLF1MA-C MARKER TIE ARE INCLUDED FOR CUSTOMER APPLIED SWITCH AND PORT IDENTIFICATION. FOR PRINTABLE LABEL OPTIONS, REFER TO PANDUIT C125X030FJJ, C125X030YPT AND C125X030FJC.
6. REFER TO 03073-06 FOR PLUG PACK CUSTOMER DRAWING.


QUICKNET PLUG PACK ASSEMBLY MATRIX

QPP	A	C	B	A	B	03
QUICKNET PLUG PACK	PERFORMANCE LEVEL	FLAME/SMOKE RATING (see notes below)	CABLE COLOR	PLUG PACK CONFIGURATION	PLUG PACK COLOR	PATCH CORD ASSEMBLY LENGTH
QPP	A - CAT 6A (10Gig) UTP	C - CM	B - BLUE	R - RECESSED 6 PACK	S - SILVER	03 = 3 FEET
	E - CAT 6A (10Gig) / CAT 6 STP	L - LOW SMOKE ZERO HALOGEN (LSZH)	W - WHITE*			05 = 5 FEET
	C - CAT 6 UTP	D - DUAL RATING (MEETS BOTH CM AND LSZH RATING)	G - GRAY CABLE BLACK BOOT**			07 = 7 FEET
						10 = 10 FEET
						14 = 14 FEET
						1M = 1 METER
						2M = 2 METERS
						3M = 3 METERS
						5M = 5 METERS

NOTES (FLAME RATING ABOVE):

- 1) ALL UTP ASSEMBLIES AVAILABLE IN CM OR LSZH ONLY (NO DUAL RATED OPTION AVAILABLE).
- 2) ALL STP ASSEMBLIES AVAILABLE ONLY AS DUAL RATED-D (MEET BOTH CM + LSZH REQUIREMENTS).

- * NOT AVAILABLE IN CAT6A/CAT6 STP
- ** ONLY AVAILABLE IN CAT6A/CAT6 STP



PART NUMBER		QPP***RS**	
TITLE			
QUICKNET RECESSED 6 POSITION PLUG PACK ASSEMBLY			
CUSTOMER DRAWING			
ITEM REVISION NAME		M03073AB/00	
DATASET FILE NAME		M03073AB_DC05/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		PANDUIT MATERIAL:	
.x ± .xxx ± .010 [.3] .xx ± .03 [.8] ANGLES ±			
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
03073-05		03073-05	
DRAWN BY	DATE	CHK	SCALE
MDJR	11-03-08	WFM1	NONE
SHT 1 OF 1		A	