





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ISOMETRIC VIEW

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. REFERENCE TIA-568-C.O. FOR DETAILS ON METHOD A CONNECTIVITY.
4. MATERIALS:
 - A. BOX AND LID: ALUMINUM
 - B. ADAPTERS: COMPOSITE PLASTIC
5. CASSETTE MODULE WEIGHT: 37.0oz [1050.0g]
6. DIMENSIONS IN BRACKETS ARE METRIC
7. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

							TITLE HDQ SERIES FIBER OPTIC FLAT CASSETTES FOR BROCADE 64 PORTS (128 FIBERS)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 12F193AA/02					
							DATASET FILE NAME 12F193AA_DC/02B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±			MATERIAL:		
							 THIRD ANGLE PROJECTION			DRAWING NUMBER: 12F193AA-DC		
01	09-24-13	SAT	YMG		RELEASED TO PRODUCTION	12F193AA-DC	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 3	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SAT	05-15-13	YMG	NONE	SIZE A	

B

