




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DUPLEX LC → 1 2 3 4
PORTS


VIEW SHOWN WITHOUT
DUSTCAPS



PANDUIT PART NUMBER	FIBER TYPE	PERFORMANCE LEVEL	MPO GENDER
FQ3XN-08-10NMBN	OM3	STANDARD LOSS	MALE
FQ3XO-08-10NMBN	OM3	OPTIMIZED LOSS	MALE
FQ3ZN-08-10NMBN	OM4	STANDARD LOSS	MALE
FQ3ZO-08-10NMBN	OM4	OPTIMIZED LOSS	MALE

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
 - A. MODULE MATERIAL: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 2.4oz (69.0g)
5. DIMENSIONS IN BRACKETS ARE METRIC
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

							TITLE QUICKNET SFQ SERIES CASSETTE, 40G-10G DUPLEX LC TO MPO MIGRATION CASSETTE					
							CUSTOMER DRAWING					
							ITEM REVISION NAME 13F244AA/00				PANDUIT	
							DATASET FILE NAME 13F244AA_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±				MATERIAL: SEE NOTE 3	
							 THIRD ANGLE PROJECTION				DRAWING NUMBER: 13F244AA-DC	
00	12-20-13	BSN	WJM	ALMY	RELEASED TO PRODUCTION	13F244AA-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BSN	DATE 12-20-13	CHK WJM	SCALE 1:2	SHT 1 OF 1	SIZE A