



| | | | | | | | | | | | | |
|-----|----------|-----|-----|-----|------------------------|-------------|---|----------|--|-------|---|--|
| | | | | | | | TITLE | | PANMPO TO LC UNIBOOT HARNESS (HYDRA) CABLE ASSEMBLY | | | |
| | | | | | | | | | CUSTOMER DRAWING | | | |
| | | | | | | | ITEM REVISION NAME | | M02680FT/00 | |  | |
| | | | | | | | DATASET FILE NAME | | M02680FT_DC/00A | | | |
| | | | | | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | | | MATERIAL: | |
| | | | | | | | .X ± .XXX ± .010 [0.3] | | | | | |
| | | | | | | | .XX ± .03 [0.8] | | ANGLES ± | | | |
| 00 | 09-26-13 | SAT | JGD | | RELEASED TO PRODUCTION | M02680FT-DC |  | | THIRD ANGLE PROJECTION | | DRAWING NUMBER: M02680FT-DC | |
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | DRAWN BY | DATE | CHK | SCALE | SHT 1 OF 2 | |
| | | | | | | | SAT | 09-26-13 | JGD | NONE | B | |

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| | | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|----|----|----|----|----|----|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 |
| F | | | R | | 8 | N | U | | S | N | | | | |

FIBER TYPE

X - OM3
Z - OM4

FLAME COUNT

8 - 8 FIBERS
T - 12 FIBERS

FLAME RATING

L - LSZH
P - PLENUM OFNP

VARIANT END B

A - 18" EQUAL BREAKOUT D - 1 METER EQUAL BREAKOUT
B - 30" EQUAL BREAKOUT S - 24" EQUAL BREAKOUT
C - 36" EQUAL BREAKOUT K - 2 METERS EQUAL BREAKOUT

UNIT OF MEASURE

M - METERS
F - FEET

LENGTH



B

B



A

A

| | | | | | | | | | | | | | |
|-----|----------|-----|-----|-----|------------------------|-----|-----------------|------------------|-------------|---|------------|---|--|
| | | | | | | | | | | TITLE PANMPO TO LC UNIBOOT HARNESS (HYDRA) CABLE ASSEMBLY | | | |
| | | | | | | | | | | CUSTOMER DRAWING | | | |
| | | | | | | | | | | ITEM REVISION NAME M02680FT/00 | |  | |
| | | | | | | | | | | DATASET FILE NAME M02680FT_DC/00A | | | |
| | | | | | | | | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | MATERIAL: | |
| | | | | | | | | | | .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ± | | | |
| | | | | | | | | | |  | | DRAWING NUMBER: M02680FT - DC | |
| | | | | | | | | | | THIRD ANGLE PROJECTION | | | |
| 00 | 09-26-13 | SAT | JGD | | RELEASED TO PRODUCTION | | | | M02680FT-DC | | | | |
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | DRAWN BY SAT | DATE 09-26-13 | CHK JGD | SCALE NONE | SHT 2 OF 2 | SIZE B | |

2



1