





PANDUIT PART NUMBER	WEIGHT
FR1V4524X4	3.94 LB/EACH (1787g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 24x4 INSIDE VERTICAL 45° ANGLE FITTING IS DESIGNED WITH A MINIMUM 3" (76.2) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. THE FIBERRUNNER 24x4 INSIDE VERTICAL 45° ANGLE FITTING INCLUDES:
ONE (1) INSIDE VERTICAL 45° ANGLE BASE
ONE (1) INSIDE VERTICAL 45° ANGLE COVER
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39701CO_DC/00 FRIV4524X4

CAD_FILENAME/LAYERS

FRI V4524X4.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER 24x4 INSIDE VERTICAL
45° ANGLE FITTING (FRIV4524X4)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X)	±	(.XXX)	±
(.XX)	±.03	(.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	MSO
DATE	10-21-08
CHK'D	SL

MAT'L:	
--------	--

ABS

SCALE	NONE
-------	------

DRAWING NO.
39701-23

DWG
A
SIZE

R	10-21-08	MSO	SL	RELEASED TO PRODUCTION	39701-23	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB