

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART#	DESCRIPTION	WEIGHT*
CJE5E88TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. RED WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.73 LB/100 PCS (785g/100 PCS)

\*WEIGHT IS APPROXIMATE  
\*\*JACK COLOR SUFFIX



NOTES:


- JACK MODULE USES SEALANT(S) TO PROTECT CONTACTS FROM CORROSION AND CONTAMINATION.
- RED WIRE CAP DESIGNATES CATEGORY 5e PERFORMANCE.
- TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- MATERIAL:  
MODULE HOUSING - PBT  
WIRE CAP - PC  
STRAIN RELIEF CLIP - PC
- ALL TX5e CAT5e 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME	M01874AA/00	SIZE
DRAWING FILENAME	M02115AA_DC13/00B	A

TX5e CAT5e CORROSIVE RESISTANT  
JACK MODULE CUSTOMER DRAWING

**PANDUIT**  
TINLEY PARK, IL 60487



ALL DIMENSIONS ARE GIVEN IN INCHES,  
UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ±.010(.3)  
(.XX) ±.03(.8) ANGLES ±

I.I. NUMBER
PRODUCT SPEC/ PKG SPEC
ASSY METHOD/ TEST METHOD
SCALE FULL
PART NO. CJE5E88TG**
DRAWING NO. 02115-13

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	6-4-10	BJN	KAA	B. UPDATED TITLE BLOCK A. UPDATED WEIGHT	02115-13		PBD		
R	6-04-09	MDJr	AGF	RELEASED TO PRODUCTION	02115-13		PBD		

DRAWN BY MDJr	REVIEW DRAWING NUMBERS
DATE 3-18-09	MAT'L
CHK'D AGF	