


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CNDS40	50 LBS/EACH 22.7 Kg/EACH



- NOTES:
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 - PARTS SUPPLIED:
1 - HANDLE SIDE SECTION
1 - HEADER SIDE SECTION
 - DIMENSIONS IN PARENTHESIS ARE METRIC

MODEL FILENAME		09V123ZS/02.PRT	
CAD FILENAME/LAYERS		09V123ZS_DC/02A.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
40" WIDE SPLIT DOORS CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.03	X. +/- 0.8	ALL DIMENSIONS ARE GIVEN	
X.XX +/- 0.015	X.X +/- 0.4	IN INCHES, THIRD ANGLE PROJECTION.	
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY MRWA	MAT'L:	SCALE NONE	
DATE 1-28-11		DRAWING NO.	DWG A SIZE
CHK'D ANI		09V123ZS-DC	

O2A	1-28-11	MRWA	ANI	RELEASED TO PRODUCTION	09V123ZS-DC				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH