



REAR VIEW



FRONT VIEW



SIDE VIEW

PLUG
30 AMP, 250V
TWIST-LOCK
NEMA L6-30P

TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.

THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN

DATE

PRINT

TITLE

SMARTZONE GATEWAY-ENABLED M SERIES RACK PDU

GM-A0252BL

CUSTOMER DRAWING

ITEM REVISION NAME

AA0252AP/01.PRT

DATASET FILE NAME

AA0252CP_DC/01A.PRT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:

INCHES	+/-	METRIC - MILLIMETER	ANGLE
X.X	+/-	X.X	+/-
X.XX	+/-	X.X	+/-
X.XXX	+/-	X.XX	+/-

THIRD ANGLE PROJECTION

DRAWN BY

GLM

DATE

10-22-14

CHK

GLM

SCALE

NONE

MATERIAL/COLOR:

N/A

DRAWING NUMBER:

AA0252CP_DC

SHT 1 OF 1

SIZE

B

- NOTES:
- IDENTIFICATION: VERTICAL, MIXED (24) C13 & (6) C19, GATEWAY-ENABLE MONITORED, 208V / 30A / SINGLE-PHASE PDU
 - ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
 - INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CONNECTION TO GATEWAY, DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY.
 - RoHS COMPLIANT.
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 - MAXIMUM AVAILABLE INPUT POWER = 4.9 kW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
 - PRINTED WITH CURCUIT IDENTIFICATION

PART NO. COLOR
GM-A0252BL BLACK