

2






1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
GM-A0270BL	6.80kg (15.0lb)

- NOTES:
1. IDENTIFICATION: VERTICAL, (24) NEMA 5-20R, GATEWAY-ENABLED MONITORED, 120V / 20A / SINGLE PHASE PDU  

PART NO.	COLOR
GM-A0270BL	BLACK
  2. ACCESSORY COMPONENTS:  
(1) QUICK-START GUIDE
  3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
  4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY
  5. RoHS COMPLIANT
  6. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
  7. MAXIMUM AVAILABLE INPUT POWER = 1.9 kW
  8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
  9. PRINTED WITH CIRCUIT IDENTIFICATION



PLUG  
20 AMP, 125V  
TWIST-LOCK  
NEMA L5-20P

TWENTY-FOUR (24)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20R

01A	03/10/15	PJST	MRWA	EDM	REVISED DISPLAY ORIENTATION	AA0270CP
00A	11/04/14	MIM	MRWA	EDM	RELEASED TO PRODUCTION	AA0270CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE SMARTZONE GATEWAY-ENABLED M SERIES RACK PDU GM-A0270BL CUSTOMER DRAWING			
ITEM REVISION NAME AA0270AP/01.PRT			
DATASET FILE NAME AA0270CP_DC/01A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/-, X.XX +/-, X.XXX +/- METRIC - MILLIMETER X.X +/-, X.XX +/- ANGLE +/-		MATERIAL/COLOR: N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER: AA0270CP_DC	
DRAWN BY PJST	DATE 03/26/14	CHK MRWA	SCALE 1:8
SHT 1 OF 1		SIZE B	