


PANDUIT P/N	WEIGHT
H1B1B1A0A10AJA0	4.31kg (9.51lb)


NOTES:
1. IDENTIFICATION: HORIZONTAL, (10) NEMA 5-15R, BASIC, 120V / 15A / SINGLE-PHASE PDU

PART NO. H1B1B1A0A10AJA0 COLOR BLACK


2. ACCESSORY COMPONENTS:
 (1) QUICK-START GUIDE
 (4) #12-24 SCREWS
 (4) M6 x 20mm SCREWS
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. RoHS COMPLIANT
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
6. MAXIMUM AVAILABLE INPUT POWER = 1.4 kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



FRONT VIEW




REAR VIEW



SIDE VIEW



PLUG
15 AMP, 125V
STRAIGHT BLADE
NEMA 5-15P



TEN (10)
RECEPTACLES
15 AMP, 125V
STRAIGHT BLADE
NEMA 5-15R

00A	09-19-14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V092DF-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
BASIC PDU (10) 5-15R CUSTOMER DRAWING			
ITEM REVISION NAME		12V092DF/00	
DATASET FILE NAME		12V092DF_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	ANGLE	
X.X +/- 0.03	X. +/- 0.8	+/- 1°	
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
DRAWN BY		DATE	CHK
SAT		09-16-14	MRWA
SCALE		NONE	
DRAWING NUMBER:		SHT 1 OF 1	
12V092DF-DC		SIZE	
		B	