


|                 |                 |
|-----------------|-----------------|
| PANDUIT P/N     | WEIGHT          |
| H1B1B1COA10AKA0 | 3.5kg (7.74lbs) |


NOTES:  
1. IDENTIFICATION: HORIZONTAL, (10) NEMA 5-20R, BASIC, 120V / 20A / SINGLE-PHASE PDU

PART NO. H1B1B1COA10AKA0      COLOR BLACK


2. ACCESSORY COMPONENTS:  
    (1) QUICK-START GUIDE  
    (4) #12-24 SCREWS  
    (4) M6 x 20mm SCREWS
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. RoHS COMPLIANT
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
6. MAXIMUM AVAILABLE INPUT POWER = 1.9 kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES




FRONT VIEW




REAR VIEW



SIDE VIEW



PLUG  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20P



TEN (10)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20R

|     |          |     |      |     |                        |             |
|-----|----------|-----|------|-----|------------------------|-------------|
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
|     |          |     |      |     |                        |             |
| 00A | 09-19-14 | SAT | MRWA | EDM | RELEASED TO PRODUCTION | 12V092DE-DC |
| REV | DATE     | BY  | CHK  | APR | DESCRIPTION            | ECN         |

|   |                     |        |                 |
|---|---------------------|--------|-----------------|
| WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.                                 |                     | SIGN   |                 |
| THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY. |                     | DATE   |                 |
|   |                     | PRINT  |                 |
| TITLE   |                     |        |                 |
| BASIC PDU<br>(10) 5-20R<br>CUSTOMER DRAWING   |                     |        |                 |
| ITEM REVISION NAME  |                     |        |                 |
| 12V092DE/00   |                     |        |                 |
| DATASET FILE NAME   |                     |        |                 |
| 12V092DE_DC/00A   |                     |        |                 |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:   |                     |        | MATERIAL/COLOR: |
| INCHES  | METRIC - MILLIMETER | ANGLE  |                 |
| X.X +/- 0.03  | X.X +/- 0.8         |        |                 |
| X.XX +/- 0.018  | X.X +/- 0.46        | +/- 1° |                 |
| X.XXX +/- 0.007   | X.XX +/- 0.18       |        |                 |
| THIRD ANGLE PROJECTION  |                     |        | DRAWING NUMBER: |
| DRAWN BY SAT DATE 09-15-14 CHK MRWA SCALE NONE  |                     |        | 12V092DE-DC     |
|   |                     |        | SHT 1 OF 1      |
|   |                     |        | SIZE B          |